



COOLING TECHNOLOGY INSTITUTE

P. O. Box 681807, Houston, Texas 77268 • 3845 Cypress Creek Parkway, Ste 420, Houston, Texas 77068
Phone: 281.583.4087 • Fax: 281.537.1721 • email: vmanser@cti.org • http://www.cti.org

August 6, 2020
(Revision 8)

Reymosa Cooling Towers, Inc.
(Div. Fabrica Mexicana De Torres, S. A.)
A. S. Palomo No. 3349 Ote.
Monterrey, N.L., Mexico C.P. 64510

Subject: CTI Cooling Tower Certification of the Reymosa RT Series Cooling Towers

Greetings:

The Reymosa Cooling Towers, Inc. RT Series line of counter-flow, induced-draft, cooling towers, as described in your original application and subsequent revisions through July 29, 2020, has satisfactorily fulfilled the requirements for certification of thermal performance by the Cooling Technology Institute (CTI), as set forth in the CTI Certification Standard STD-201(19). A listing of the twelve-hundred-sixty-six (1266) RT singular units (including 408 RTG single-fan, gearbox models), nine-hundred-four (904) RTM modular units (including 452 RTGM single-fan, gearbox models) and three-hundred-twelve (312) RTU, reduced height, units encompassed by the RT Series of cooling towers is included with this letter for reference.

The Reymosa Cooling Towers RT Series line of cooling towers has been assigned and should use CTI Certification Validation Number C22G-13R08. You are hereby authorized and encouraged to display the CTI Certification Logo in all pertinent literature and are required to affix the CTI Certification Label on all towers comprising the line, as provided in the Certification Standard.

This CTI Certification requires the successful completion of a CTI Annual Reverification Test on a different model each year to remain in effect in the subsequent year.

Very truly yours,

Michael Womack, P.E.
CTI Certification Administrator



COOLING TECHNOLOGY INSTITUTE

P. O. Box 681807, Houston, Texas 77268 • 3845 Cypress Creek Parkway, Ste 420, Houston, Texas 77068
Phone: 281.583.4087 • Fax: 281.537.1721 • email: vmanser@cti.org • http://www.cti.org

Reymosa Cooling Towers, Inc.
(Div. Fabrica Mexicana De Torres, S. A.)
RT Series of CTI Certified Cooling Towers
CTI Certification Validation Number C22G-13R08
August 6, 2020 (Revision 8)

RT Models (Note 1) Below are Single Units with 1, 2 or 4 Fans/Unit and 4 Air Inlet Faces/Unit

RT-30311.5-A	RT-30311.5-B			RT-30311.5-C	RT-30311.5-D		
RT-303102-A	RT-303102-B			RT-303102-C	RT-303102-D		
RT-404103-A	RT-404103-B			RT-404103-C	RT-404103-D		
RT-404105-A	RT-404105-B			RT-404105-C	RT-404105-D		
RT-505103-A	RT-505103-B			RT-505103-C	RT-505103-D		
RT-505105-A	RT-505105-B			RT-505105-C	RT-505105-D		
RT-606105-A	RT-606105-B			RT-606105-C	RT-606105-D		
RT-60617.5-A	RT-60617.5-B			RT-60617.5-C	RT-60617.5-D		
RT-707105-A	RT-707105-B	RT-707105-B-LS	RT-707105-B-SLS	RT-707105-C	RT-707105-D	RT-707105-D-LS	RT-707105-D-SLS
RT-70717.5-A	RT-70717.5-B	RT-70717.5-B-LS	RT-70717.5-B-SLS	RT-70717.5-C	RT-70717.5-D	RT-70717.5-D-LS	RT-70717.5-D-SLS
RT-707110-A	RT-707110-B	RT-707110-B-LS	RT-707110-B-SLS	RT-707110-C	RT-707110-D	RT-707110-D-LS	RT-707110-D-SLS
RT-708105-A	RT-708105-B	RT-708105-B-LS	RT-708105-B-SLS	RT-708105-C	RT-708105-D	RT-708105-D-LS	RT-708105-D-SLS
RT-70817.5-A	RT-70817.5-B	RT-70817.5-B-LS	RT-70817.5-B-SLS	RT-70817.5-C	RT-70817.5-D	RT-70817.5-D-LS	RT-70817.5-D-SLS
RT-708110-A	RT-708110-B	RT-708110-B-LS	RT-708110-B-SLS	RT-708110-C	RT-708110-D	RT-708110-D-LS	RT-708110-D-SLS
RT-708115-A	RT-708115-B	RT-708115-B-LS	RT-708115-B-SLS	RT-708115-C	RT-708115-D	RT-708115-D-LS	RT-708115-D-SLS
RT-709105-A	RT-709105-B	RT-709105-B-LS	RT-709105-B-SLS	RT-709105-C	RT-709105-D	RT-709105-D-LS	RT-709105-D-SLS
RT-70917.5-A	RT-70917.5-B	RT-70917.5-B-LS	RT-70917.5-B-SLS	RT-70917.5-C	RT-70917.5-D	RT-70917.5-D-LS	RT-70917.5-D-SLS
RT-709110-A	RT-709110-B	RT-709110-B-LS	RT-709110-B-SLS	RT-709110-C	RT-709110-D	RT-709110-D-LS	RT-709110-D-SLS
RT-709115-A	RT-709115-B	RT-709115-B-LS	RT-709115-B-SLS	RT-709115-C	RT-709115-D	RT-709115-D-LS	RT-709115-D-SLS
RT-808105-A	RT-808105-B	RT-808105-B-LS	RT-808105-B-SLS	RT-808105-C	RT-808105-D	RT-808105-D-LS	RT-808105-D-SLS
RT-80817.5-A	RT-80817.5-B	RT-80817.5-B-LS	RT-80817.5-B-SLS	RT-80817.5-C	RT-80817.5-D	RT-80817.5-D-LS	RT-80817.5-D-SLS
RT-808110-A	RT-808110-B	RT-808110-B-LS	RT-808110-B-SLS	RT-808110-C	RT-808110-D	RT-808110-D-LS	RT-808110-D-SLS
RT-808115-A	RT-808115-B	RT-808115-B-LS	RT-808115-B-SLS	RT-808115-C	RT-808115-D	RT-808115-D-LS	RT-808115-D-SLS
RT-810105-A	RT-810105-B	RT-810105-B-LS	RT-810105-B-SLS	RT-810105-C	RT-810105-D	RT-810105-D-LS	RT-810105-D-SLS
RT-81017.5-A	RT-81017.5-B	RT-81017.5-B-LS	RT-81017.5-B-SLS	RT-81017.5-C	RT-81017.5-D	RT-81017.5-D-LS	RT-81017.5-D-SLS
RT-810110-A	RT-810110-B	RT-810110-B-LS	RT-810110-B-SLS	RT-810110-C	RT-810110-D	RT-810110-D-LS	RT-810110-D-SLS
RT-810115-A	RT-810115-B	RT-810115-B-LS	RT-810115-B-SLS	RT-810115-C	RT-810115-D	RT-810115-D-LS	RT-810115-D-SLS
RT-810120-A	RT-810120-B	RT-810120-B-LS	RT-810120-B-SLS	RT-810120-C	RT-810120-D	RT-810120-D-LS	RT-810120-D-SLS
RT-812105-A	RT-812105-B	RT-812105-B-LS	RT-812105-B-SLS	RT-812105-C	RT-812105-D	RT-812105-D-LS	RT-812105-D-SLS
RT-81217.5-A	RT-81217.5-B	RT-81217.5-B-LS	RT-81217.5-B-SLS	RT-81217.5-C	RT-81217.5-D	RT-81217.5-D-LS	RT-81217.5-D-SLS
RT-812110-A	RT-812110-B	RT-812110-B-LS	RT-812110-B-SLS	RT-812110-C	RT-812110-D	RT-812110-D-LS	RT-812110-D-SLS
RT-812115-A	RT-812115-B	RT-812115-B-LS	RT-812115-B-SLS	RT-812115-C	RT-812115-D	RT-812115-D-LS	RT-812115-D-SLS
RT-812120-A	RT-812120-B	RT-812120-B-LS	RT-812120-B-SLS	RT-812120-C	RT-812120-D	RT-812120-D-LS	RT-812120-D-SLS
RT-812125-A	RT-812125-B	RT-812125-B-LS	RT-812125-B-SLS	RT-812125-C	RT-812125-D	RT-812125-D-LS	RT-812125-D-SLS

RT Models Continued on Next Page



COOLING TECHNOLOGY INSTITUTE

P. O. Box 681807, Houston, Texas 77268 • 3845 Cypress Creek Parkway, Ste 420, Houston, Texas 77068
Phone: 281.583.4087 • Fax: 281.537.1721 • email: vmanser@cti.org • http://www.cti.org

RT Models (Note 1) Below are Double Units with 1, 2 or 4 Fans/Unit and 4 Air Inlet Faces/Unit

RT-714205-A	RT-714205-B	RT-714205-B-LS	RT-714205-B-SLS	RT-714205-C	RT-714205-D	RT-714205-D-LS	RT-714205-D-SLS
RT-71427.5-A	RT-71427.5-B	RT-71427.5-B-LS	RT-71427.5-B-SLS	RT-71427.5-C	RT-71427.5-D	RT-71427.5-D-LS	RT-71427.5-D-SLS
RT-714210-A	RT-714210-B	RT-714210-B-LS	RT-714210-B-SLS	RT-714210-C	RT-714210-D	RT-714210-D-LS	RT-714210-D-SLS
RT-816205-A	RT-816205-B	RT-816205-B-LS	RT-816205-B-SLS	RT-816205-C	RT-816205-D	RT-816205-D-LS	RT-816205-D-SLS
RT-81627.5-A	RT-81627.5-B	RT-81627.5-B-LS	RT-81627.5-B-SLS	RT-81627.5-C	RT-81627.5-D	RT-81627.5-D-LS	RT-81627.5-D-SLS
RT-816210-A	RT-816210-B	RT-816210-B-LS	RT-816210-B-SLS	RT-816210-C	RT-816210-D	RT-816210-D-LS	RT-816210-D-SLS
RT-816215-A	RT-816215-B	RT-816215-B-LS	RT-816215-B-SLS	RT-816215-C	RT-816215-D	RT-816215-D-LS	RT-816215-D-SLS
RT-819205-A	RT-819205-B	RT-819205-B-LS	RT-819205-B-SLS	RT-819205-C	RT-819205-D	RT-819205-D-LS	RT-819205-D-SLS
RT-81927.5-A	RT-81927.5-B	RT-81927.5-B-LS	RT-81927.5-B-SLS	RT-81927.5-C	RT-81927.5-D	RT-81927.5-D-LS	RT-81927.5-D-SLS
RT-819210-A	RT-819210-B	RT-819210-B-LS	RT-819210-B-SLS	RT-819210-C	RT-819210-D	RT-819210-D-LS	RT-819210-D-SLS
RT-819215-A	RT-819215-B	RT-819215-B-LS	RT-819215-B-SLS	RT-819215-C	RT-819215-D	RT-819215-D-LS	RT-819215-D-SLS
RT-819220-A	RT-819220-B	RT-819220-B-LS	RT-819220-B-SLS	RT-819220-C	RT-819220-D	RT-819220-D-LS	RT-819220-D-SLS
RT-822205-A	RT-822205-B	RT-822205-B-LS	RT-822205-B-SLS	RT-822205-C	RT-822205-D	RT-822205-D-LS	RT-822205-D-SLS
RT-82227.5-A	RT-82227.5-B	RT-82227.5-B-LS	RT-82227.5-B-SLS	RT-82227.5-C	RT-82227.5-D	RT-82227.5-D-LS	RT-82227.5-D-SLS
RT-822210-A	RT-822210-B	RT-822210-B-LS	RT-822210-B-SLS	RT-822210-C	RT-822210-D	RT-822210-D-LS	RT-822210-D-SLS
RT-822215-A	RT-822215-B	RT-822215-B-LS	RT-822215-B-SLS	RT-822215-C	RT-822215-D	RT-822215-D-LS	RT-822215-D-SLS
RT-822220-A	RT-822220-B	RT-822220-B-LS	RT-822220-B-SLS	RT-822220-C	RT-822220-D	RT-822220-D-LS	RT-822220-D-SLS
RT-822225-A	RT-822225-B	RT-822225-B-LS	RT-822225-B-SLS	RT-822225-C	RT-822225-D	RT-822225-D-LS	RT-822225-D-SLS
RT-824205-A	RT-824205-B	RT-824205-B-LS	RT-824205-B-SLS	RT-824205-C	RT-824205-D	RT-824205-D-LS	RT-824205-D-SLS
RT-82427.5-A	RT-82427.5-B	RT-82427.5-B-LS	RT-82427.5-B-SLS	RT-82427.5-C	RT-82427.5-D	RT-82427.5-D-LS	RT-82427.5-D-SLS
RT-824210-A	RT-824210-B	RT-824210-B-LS	RT-824210-B-SLS	RT-824210-C	RT-824210-D	RT-824210-D-LS	RT-824210-D-SLS
RT-824215-A	RT-824215-B	RT-824215-B-LS	RT-824215-B-SLS	RT-824215-C	RT-824215-D	RT-824215-D-LS	RT-824215-D-SLS
RT-824220-A	RT-824220-B	RT-824220-B-LS	RT-824220-B-SLS	RT-824220-C	RT-824220-D	RT-824220-D-LS	RT-824220-D-SLS
RT-824225-A	RT-824225-B	RT-824225-B-LS	RT-824225-B-SLS	RT-824225-C	RT-824225-D	RT-824225-D-LS	RT-824225-D-SLS
RT-827205-A	RT-827205-B	RT-827205-B-LS	RT-827205-B-SLS	RT-827205-C	RT-827205-D	RT-827205-D-LS	RT-827205-D-SLS
RT-82727.5-A	RT-82727.5-B	RT-82727.5-B-LS	RT-82727.5-B-SLS	RT-82727.5-C	RT-82727.5-D	RT-82727.5-D-LS	RT-82727.5-D-SLS
RT-827210-A	RT-827210-B	RT-827210-B-LS	RT-827210-B-SLS	RT-827210-C	RT-827210-D	RT-827210-D-LS	RT-827210-D-SLS
RT-827215-A	RT-827215-B	RT-827215-B-LS	RT-827215-B-SLS	RT-827215-C	RT-827215-D	RT-827215-D-LS	RT-827215-D-SLS
RT-827220-A	RT-827220-B	RT-827220-B-LS	RT-827220-B-SLS	RT-827220-C	RT-827220-D	RT-827220-D-LS	RT-827220-D-SLS
RT-827225-A	RT-827225-B	RT-827225-B-LS	RT-827225-B-SLS	RT-827225-C	RT-827225-D	RT-827225-D-LS	RT-827225-D-SLS

RT Models Continued on Next Page



COOLING TECHNOLOGY INSTITUTE

P. O. Box 681807, Houston, Texas 77268 • 3845 Cypress Creek Parkway, Ste 420, Houston, Texas 77068
Phone: 281.583.4087 • Fax: 281.537.1721 • email: vmanser@cti.org • http://www.cti.org

RT Models (Note 1) Below are Quad Units with 1, 2 or 4 Fans/Unit and 4 Air Inlet Faces/Unit

RT-1414405-A	RT-1414405-B	RT-1414405-B-LS	RT-1414405-B-SLS	RT-1414405-C	RT-1414405-D	RT-1414405-D-LS	RT-1414405-D-SLS
RT-141447.5-A	RT-141447.5-B	RT-141447.5-B-LS	RT-141447.5-B-SLS	RT-141447.5-C	RT-141447.5-D	RT-141447.5-D-LS	RT-141447.5-D-SLS
RT-1414410-A	RT-1414410-B	RT-1414410-B-LS	RT-1414410-B-SLS	RT-1414410-C	RT-1414410-D	RT-1414410-D-LS	RT-1414410-D-SLS
RT-1616405-A	RT-1616405-B	RT-1616405-B-LS	RT-1616405-B-SLS	RT-1616405-C	RT-1616405-D	RT-1616405-D-LS	RT-1616405-D-SLS
RT-161647.5-A	RT-161647.5-B	RT-161647.5-B-LS	RT-161647.5-B-SLS	RT-161647.5-C	RT-161647.5-D	RT-161647.5-D-LS	RT-161647.5-D-SLS
RT-1616410-A	RT-1616410-B	RT-1616410-B-LS	RT-1616410-B-SLS	RT-1616410-C	RT-1616410-D	RT-1616410-D-LS	RT-1616410-D-SLS
RT-1616415-A	RT-1616415-B	RT-1616415-B-LS	RT-1616415-B-SLS	RT-1616415-C	RT-1616415-D	RT-1616415-D-LS	RT-1616415-D-SLS
RT-1619405-A	RT-1619405-B	RT-1619405-B-LS	RT-1619405-B-SLS	RT-1619405-C	RT-1619405-D	RT-1619405-D-LS	RT-1619405-D-SLS
RT-161947.5-A	RT-161947.5-B	RT-161947.5-B-LS	RT-161947.5-B-SLS	RT-161947.5-C	RT-161947.5-D	RT-161947.5-D-LS	RT-161947.5-D-SLS
RT-1619410-A	RT-1619410-B	RT-1619410-B-LS	RT-1619410-B-SLS	RT-1619410-C	RT-1619410-D	RT-1619410-D-LS	RT-1619410-D-SLS
RT-1619415-A	RT-1619415-B	RT-1619415-B-LS	RT-1619415-B-SLS	RT-1619415-C	RT-1619415-D	RT-1619415-D-LS	RT-1619415-D-SLS
RT-1619420-A	RT-1619420-B	RT-1619420-B-LS	RT-1619420-B-SLS	RT-1619420-C	RT-1619420-D	RT-1619420-D-LS	RT-1619420-D-SLS
RT-1622405-A	RT-1622405-B	RT-1622405-B-LS	RT-1622405-B-SLS	RT-1622405-C	RT-1622405-D	RT-1622405-D-LS	RT-1622405-D-SLS
RT-162247.5-A	RT-162247.5-B	RT-162247.5-B-LS	RT-162247.5-B-SLS	RT-162247.5-C	RT-162247.5-D	RT-162247.5-D-LS	RT-162247.5-D-SLS
RT-1622410-A	RT-1622410-B	RT-1622410-B-LS	RT-1622410-B-SLS	RT-1622410-C	RT-1622410-D	RT-1622410-D-LS	RT-1622410-D-SLS
RT-1622415-A	RT-1622415-B	RT-1622415-B-LS	RT-1622415-B-SLS	RT-1622415-C	RT-1622415-D	RT-1622415-D-LS	RT-1622415-D-SLS
RT-1622420-A	RT-1622420-B	RT-1622420-B-LS	RT-1622420-B-SLS	RT-1622420-C	RT-1622420-D	RT-1622420-D-LS	RT-1622420-D-SLS
RT-1622425-A	RT-1622425-B	RT-1622425-B-LS	RT-1622425-B-SLS	RT-1622425-C	RT-1622425-D	RT-1622425-D-LS	RT-1622425-D-SLS
RT-1624405-A	RT-1624405-B	RT-1624405-B-LS	RT-1624405-B-SLS	RT-1624405-C	RT-1624405-D	RT-1624405-D-LS	RT-1624405-D-SLS
RT-162447.5-A	RT-162447.5-B	RT-162447.5-B-LS	RT-162447.5-B-SLS	RT-162447.5-C	RT-162447.5-D	RT-162447.5-D-LS	RT-162447.5-D-SLS
RT-1624410-A	RT-1624410-B	RT-1624410-B-LS	RT-1624410-B-SLS	RT-1624410-C	RT-1624410-D	RT-1624410-D-LS	RT-1624410-D-SLS
RT-1624415-A	RT-1624415-B	RT-1624415-B-LS	RT-1624415-B-SLS	RT-1624415-C	RT-1624415-D	RT-1624415-D-LS	RT-1624415-D-SLS
RT-1624420-A	RT-1624420-B	RT-1624420-B-LS	RT-1624420-B-SLS	RT-1624420-C	RT-1624420-D	RT-1624420-D-LS	RT-1624420-D-SLS
RT-1624425-A	RT-1624425-B	RT-1624425-B-LS	RT-1624425-B-SLS	RT-1624425-C	RT-1624425-D	RT-1624425-D-LS	RT-1624425-D-SLS
RT-1627405-A	RT-1627405-B	RT-1627405-B-LS	RT-1627405-B-SLS	RT-1627405-C	RT-1627405-D	RT-1627405-D-LS	RT-1627405-D-SLS
RT-162747.5-A	RT-162747.5-B	RT-162747.5-B-LS	RT-162747.5-B-SLS	RT-162747.5-C	RT-162747.5-D	RT-162747.5-D-LS	RT-162747.5-D-SLS
RT-1627410-A	RT-1627410-B	RT-1627410-B-LS	RT-1627410-B-SLS	RT-1627410-C	RT-1627410-D	RT-1627410-D-LS	RT-1627410-D-SLS
RT-1627415-A	RT-1627415-B	RT-1627415-B-LS	RT-1627415-B-SLS	RT-1627415-C	RT-1627415-D	RT-1627415-D-LS	RT-1627415-D-SLS
RT-1627420-A	RT-1627420-B	RT-1627420-B-LS	RT-1627420-B-SLS	RT-1627420-C	RT-1627420-D	RT-1627420-D-LS	RT-1627420-D-SLS
RT-1627425-A	RT-1627425-B	RT-1627425-B-LS	RT-1627425-B-SLS	RT-1627425-C	RT-1627425-D	RT-1627425-D-LS	RT-1627425-D-SLS

RT Models Continued on Next Page



COOLING TECHNOLOGY INSTITUTE

P. O. Box 681807, Houston, Texas 77268 • 3845 Cypress Creek Parkway, Ste 420, Houston, Texas 77068
 Phone: 281.583.4087 • Fax: 281.537.1721 • email: vmanser@cti.org • http://www.cti.org

RT Models (Note 1) Below are Single or Double Units with Direct Drive (PM) Fan(s)

RTP-707105-B	RTP-714205-B	RTP-707105-D	RTP-714205-D	RTP-1414405-B	RTP-1414405-D
RTP-70717.5-B	RTP-71427.5-B	RTP-70717.5-D	RTP-71427.5-D	RTP-141447.5-B	RTP-141447.5-D
RTP-707110-B	RTP-714210-B	RTP-707110-D	RTP-714210-D	RTP-1414410-B	RTP-1414410-D
RTP-708105-B	RTP-816205-B	RTP-708105-D	RTP-816205-D	RTP-1616405-B	RTP-1616405-D
RTP-70817.5-B	RTP-81627.5-B	RTP-70817.5-D	RTP-81627.5-D	RTP-161647.5-B	RTP-161647.5-D
RTP-708110-B	RTP-816210-B	RTP-708110-D	RTP-816210-D	RTP-1616410-B	RTP-1616410-D
RTP-708115-B	RTP-816215-B	RTP-708115-D	RTP-816215-D	RTP-1616415-B	RTP-1616415-D
RTP-709105-B	RTP-819205-B	RTP-709105-D	RTP-819205-D	RTP-1619405-B	RTP-1619405-D
RTP-70917.5-B	RTP-81927.5-B	RTP-70917.5-D	RTP-81927.5-D	RTP-161947.5-B	RTP-161947.5-D
RTP-709110-B	RTP-819210-B	RTP-709110-D	RTP-819210-D	RTP-1619410-B	RTP-1619410-D
RTP-709115-B	RTP-819215-B	RTP-709115-D	RTP-819215-D	RTP-1619415-B	RTP-1619415-D
RTP-808105-B	RTP-822205-B	RTP-808105-D	RTP-822205-D	RTP-1622405-B	RTP-1622405-D
RTP-80817.5-B	RTP-82227.5-B	RTP-80817.5-D	RTP-82227.5-D	RTP-162247.5-B	RTP-162247.5-D
RTP-808110-B	RTP-822210-B	RTP-808110-D	RTP-822210-D	RTP-1622410-B	RTP-1622410-D
RTP-808115-B	RTP-822215-B	RTP-808115-D	RTP-822215-D	RTP-1622415-B	RTP-1622415-D
RTP-810105-B	RTP-824205-B	RTP-810105-D	RTP-824205-D	RTP-1624405-B	RTP-1624405-D
RTP-81017.5-B	RTP-82427.5-B	RTP-81017.5-D	RTP-82427.5-D	RTP-162447.5-B	RTP-162447.5-D
RTP-810110-B	RTP-824210-B	RTP-810110-D	RTP-824210-D	RTP-1624410-B	RTP-1624410-D
RTP-810115-B	RTP-824215-B	RTP-810115-D	RTP-824215-D	RTP-1624415-B	RTP-1624415-D
RTP-812105-B	RTP-827205-B	RTP-812105-D	RTP-827205-D	RTP-1627405-B	RTP-1627405-D
RTP-81217.5-B	RTP-82727.5-B	RTP-81217.5-D	RTP-82727.5-D	RTP-162747.5-B	RTP-162747.5-D
RTP-812110-B	RTP-827210-B	RTP-812110-D	RTP-827210-D	RTP-1627410-B	RTP-1627410-D
RTP-812115-B	RTP-827215-B	RTP-812115-D	RTP-827215-D	RTP-1627415-B	RTP-1627415-D

RT Models Continued on Next Page



COOLING TECHNOLOGY INSTITUTE

P. O. Box 681807, Houston, Texas 77268 • 3845 Cypress Creek Parkway, Ste 420, Houston, Texas 77068
 Phone: 281.583.4087 • Fax: 281.537.1721 • email: vmanser@cti.org • http://www.cti.org

RT Models (Note 1) Below are Single Units with 1 Fan/Unit and 4 Air Inlet Faces/Unit

RTG-812103-B	RTG-1014103-A	RTG-1016103-A	RTG-1018103-A	RTG-1020103-A	RTG-1212105-A
RTG-812105-B	RTG-1014105-A	RTG-1016105-A	RTG-1018105-A	RTG-1020105-A	RTG-121217.5-A
RTG-81217.5-B	RTG-101417.5-A	RTG-101617.5-A	RTG-101817.5-A	RTG-102017.5-A	RTG-1212110-A
RTG-812110-B	RTG-1014110-A	RTG-1016110-A	RTG-1018110-A	RTG-1020110-A	RTG-1212115-A
RTG-812115-B	RTG-1014115-A	RTG-1016115-A	RTG-1018115-A	RTG-1020115-A	RTG-1212120-A
RTG-812120-B	RTG-1014120-A	RTG-1016120-A	RTG-1018120-A	RTG-1020120-A	RTG-1212125-A
RTG-812125-B	RTG-1014125-A	RTG-1016125-A	RTG-1018125-A	RTG-1020125-A	
RTG-812130-B		RTG-1016130-A	RTG-1018130-A	RTG-1020130-A	RTG-1212105-B
	RTG-1014103-B		RTG-1018140-A	RTG-1020140-A	RTG-121217.5-B
RTG-812103-D	RTG-1014105-B	RTG-1016103-B			RTG-1212110-B
RTG-812105-D	RTG-101417.5-B	RTG-1016105-B	RTG-1018103-B	RTG-1020103-B	RTG-1212115-B
RTG-81217.5-D	RTG-1014110-B	RTG-101617.5-B	RTG-1018105-B	RTG-1020105-B	RTG-1212120-B
RTG-812110-D	RTG-1014115-B	RTG-1016110-B	RTG-101817.5-B	RTG-102017.5-B	RTG-1212125-B
RTG-812115-D	RTG-1014120-B	RTG-1016115-B	RTG-1018110-B	RTG-1020110-B	RTG-1212130-B
RTG-812120-D	RTG-1014125-B	RTG-1016120-B	RTG-1018115-B	RTG-1020115-B	
RTG-812125-D	RTG-1014130-B	RTG-1016125-B	RTG-1018120-B	RTG-1020120-B	RTG-1212105-C
RTG-812130-D		RTG-1016130-B	RTG-1018125-B	RTG-1020125-B	RTG-121217.5-C
	RTG-1014103-C	RTG-1016140-B	RTG-1018130-B	RTG-1020130-B	RTG-1212110-C
RTG-1012103-A	RTG-1014105-C		RTG-1018140-B	RTG-1020140-B	RTG-1212115-C
RTG-1012105-A	RTG-101417.5-C	RTG-1016103-C		RTG-1020150-B	RTG-1212120-C
RTG-101217.5-A	RTG-1014110-C	RTG-1016105-C	RTG-1018103-C		RTG-1212125-C
RTG-1012110-A	RTG-1014115-C	RTG-101617.5-C	RTG-1018105-C	RTG-1020103-C	RTG-1212130-C
RTG-1012115-A	RTG-1014120-C	RTG-1016110-C	RTG-101817.5-C	RTG-1020105-C	
RTG-1012120-A	RTG-1014125-C	RTG-1016115-C	RTG-1018110-C	RTG-102017.5-C	RTG-1212105-D
RTG-1012125-A	RTG-1014130-C	RTG-1016120-C	RTG-1018115-C	RTG-1020110-C	RTG-121217.5-D
		RTG-1016125-C	RTG-1018120-C	RTG-1020115-C	RTG-1212110-D
RTG-1012103-B	RTG-1014103-D	RTG-1016130-C	RTG-1018125-C	RTG-1020120-C	RTG-1212115-D
RTG-1012105-B	RTG-1014105-D		RTG-1018130-C	RTG-1020125-C	RTG-1212120-D
RTG-101217.5-B	RTG-101417.5-D	RTG-1016103-D	RTG-1018140-C	RTG-1020130-C	RTG-1212125-D
RTG-1012110-B	RTG-1014110-D	RTG-1016105-D		RTG-1020140-C	RTG-1212130-D
RTG-1012115-B	RTG-1014115-D	RTG-101617.5-D	RTG-1018103-D	RTG-1020150-C	RTG-1212140-D
RTG-1012120-B	RTG-1014120-D	RTG-1016110-D	RTG-1018105-D		
RTG-1012125-B	RTG-1014125-D	RTG-1016115-D	RTG-101817.5-D	RTG-1020103-D	
RTG-1012130-B	RTG-1014130-D	RTG-1016120-D	RTG-1018110-D	RTG-1020105-D	
	RTG-1014140-D	RTG-1016125-D	RTG-1018115-D	RTG-102017.5-D	
RTG-1012103-C		RTG-1016130-D	RTG-1018120-D	RTG-1020110-D	
RTG-1012105-C		RTG-1016140-D	RTG-1018125-D	RTG-1020115-D	
RTG-101217.5-C			RTG-1018130-D	RTG-1020120-D	
RTG-1012110-C			RTG-1018140-D	RTG-1020125-D	
RTG-1012115-C			RTG-1018150-D	RTG-1020130-D	
RTG-1012120-C				RTG-1020140-D	
RTG-1012125-C				RTG-1020150-D	
				RTG-1020160-D	
RTG-1012103-D					
RTG-1012105-D					
RTG-101217.5-D					
RTG-1012110-D					
RTG-1012115-D					
RTG-1012120-D					
RTG-1012125-D					
RTG-1012130-D					

RT Models Continued on Next Page



COOLING TECHNOLOGY INSTITUTE

P. O. Box 681807, Houston, Texas 77268 • 3845 Cypress Creek Parkway, Ste 420, Houston, Texas 77068
Phone: 281.583.4087 • Fax: 281.537.1721 • email: vmanser@cti.org • http://www.cti.org

Reymosa Cooling Towers, Inc.
(Div. Fabrica Mexicana De Torres, S. A.)
RT Series of CTI Certified Cooling Towers
CTI Certification Validation Number C22G-13R08
August 6, 2020 (Revision 8)

RT Models (Note 1) Below are Single Units with 1 Fan/Unit and 4 Air Inlet Faces/Unit

RTG-1214105-A	RTG-1216105-A	RTG-1218105-A	RTG-1220105-A	RTG-1222105-A	RTG-1223110-E
RTG-121417.5-A	RTG-121617.5-A	RTG-121817.5-A	RTG-122017.5-A	RTG-122217.5-A	RTG-1223115-E
RTG-1214110-A	RTG-1216110-A	RTG-1218110-A	RTG-1220110-A	RTG-1222110-A	RTG-1223120-E
RTG-1214115-A	RTG-1216115-A	RTG-1218115-A	RTG-1220115-A	RTG-1222115-A	RTG-1223125-E
RTG-1214120-A	RTG-1216120-A	RTG-1218120-A	RTG-1220120-A	RTG-1222120-A	RTG-1223130-E
RTG-1214125-A	RTG-1216125-A	RTG-1218125-A	RTG-1220125-A	RTG-1222125-A	RTG-1223140-E
RTG-1214130-A	RTG-1216130-A	RTG-1218130-A	RTG-1220130-A	RTG-1222130-A	RTG-1223150-E
		RTG-1218140-A	RTG-1220140-A	RTG-1222140-A	RTG-1223160-E
			RTG-1220150-A	RTG-1222150-A	
				RTG-1222160-A	
RTG-1214105-B	RTG-1216105-B				
RTG-121417.5-B	RTG-121617.5-B	RTG-1218105-B			
RTG-1214110-B	RTG-1216110-B	RTG-121817.5-B	RTG-1220105-B		
RTG-1214115-B	RTG-1216115-B	RTG-1218110-B	RTG-122017.5-B	RTG-1222105-B	
RTG-1214120-B	RTG-1216120-B	RTG-1218115-B	RTG-1220110-B	RTG-122217.5-B	
RTG-1214125-B	RTG-1216125-B	RTG-1218120-B	RTG-1220115-B	RTG-1222110-B	
RTG-1214130-B	RTG-1216130-B	RTG-1218125-B	RTG-1220120-B	RTG-1222115-B	
RTG-1214140-B	RTG-1216140-B	RTG-1218130-B	RTG-1220125-B	RTG-1222120-B	
		RTG-1218140-B	RTG-1220130-B	RTG-1222125-B	
		RTG-1218150-B	RTG-1220140-B	RTG-1222130-B	
RTG-1214105-C	RTG-1216105-C		RTG-1220150-B	RTG-1222140-B	
RTG-121417.5-C	RTG-121617.5-C		RTG-1220160-B	RTG-1222150-B	
RTG-1214110-C	RTG-1216110-C	RTG-1218105-C		RTG-1222160-B	
RTG-1214115-C	RTG-1216115-C	RTG-121817.5-C		RTG-1222175-B	
RTG-1214120-C	RTG-1216120-C	RTG-1218110-C	RTG-1220105-C		
RTG-1214125-C	RTG-1216125-C	RTG-1218115-C	RTG-122017.5-C		
RTG-1214130-C	RTG-1216130-C	RTG-1218120-C	RTG-1220110-C	RTG-1222105-C	
RTG-1214140-C	RTG-1216140-C	RTG-1218125-C	RTG-1220115-C	RTG-122217.5-C	
		RTG-1218130-C	RTG-1220120-C	RTG-1222110-C	
RTG-1214105-D	RTG-1216105-D	RTG-1218140-C	RTG-1220125-C	RTG-1222115-C	
RTG-121417.5-D	RTG-121617.5-D	RTG-1218150-C	RTG-1220130-C	RTG-1222120-C	
RTG-1214110-D	RTG-1216110-D		RTG-1220140-C	RTG-1222125-C	
RTG-1214115-D	RTG-1216115-D	RTG-1218105-D	RTG-1220150-C	RTG-1222130-C	
RTG-1214120-D	RTG-1216120-D	RTG-121817.5-D	RTG-1220160-C	RTG-1222140-C	
RTG-1214125-D	RTG-1216125-D	RTG-1218110-D		RTG-1222150-C	
RTG-1214130-D	RTG-1216130-D	RTG-1218115-D	RTG-1220105-D	RTG-1222160-C	
RTG-1214140-D	RTG-1216140-D	RTG-1218120-D	RTG-122017.5-D	RTG-1222175-C	
RTG-1214150-D	RTG-1216150-D	RTG-1218125-D	RTG-1220110-D		
		RTG-1218130-D	RTG-1220115-D	RTG-1222105-D	
		RTG-1218140-D	RTG-1220120-D	RTG-122217.5-D	
		RTG-1218150-D	RTG-1220125-D	RTG-1222110-D	
		RTG-1218160-D	RTG-1220130-D	RTG-1222115-D	
			RTG-1220140-D	RTG-1222120-D	
			RTG-1220150-D	RTG-1222125-D	
			RTG-1220160-D	RTG-1222130-D	
			RTG-1220175-D	RTG-1222140-D	
				RTG-1222150-D	
				RTG-1222160-D	
				RTG-1222175-D	

RT Models Concluded



COOLING TECHNOLOGY INSTITUTE

P. O. Box 681807, Houston, Texas 77268 • 3845 Cypress Creek Parkway, Ste 420, Houston, Texas 77068
Phone: 281.583.4087 • Fax: 281.537.1721 • email: vmanser@cti.org • http://www.cti.org

Reymosa Cooling Towers, Inc.
(Div. Fabrica Mexicana De Torres, S. A.)
RT Series of CTI Certified Cooling Towers
CTI Certification Validation Number C22G-13R08
August 6, 2020 (Revision 8)

RTM Models (Note 2) Below are Modular Units with 2 Fans/Unit and 2 or 3 Air Inlet Faces/Unit

RTM-714205-B-T1	RTM-714205-B-T2	RTM-714205-B-T1-LS	RTM-714205-B-T2-LS	RTM-714205-B-T1-SLS	RTM-714205-B-T2-SLS
RTM-71427.5-B-T1	RTM-71427.5-B-T2	RTM-71427.5-B-T1-LS	RTM-71427.5-B-T2-LS	RTM-71427.5-B-T1-SLS	RTM-71427.5-B-T2-SLS
RTM-714210-B-T1	RTM-714210-B-T2	RTM-714210-B-T1-LS	RTM-714210-B-T2-LS	RTM-714210-B-T1-SLS	RTM-714210-B-T2-SLS
RTM-816205-B-T1	RTM-816205-B-T2	RTM-816205-B-T1-LS	RTM-816205-B-T2-LS	RTM-816205-B-T1-SLS	RTM-816205-B-T2-SLS
RTM-81627.5-B-T1	RTM-81627.5-B-T2	RTM-81627.5-B-T1-LS	RTM-81627.5-B-T2-LS	RTM-81627.5-B-T1-SLS	RTM-81627.5-B-T2-SLS
RTM-816210-B-T1	RTM-816210-B-T2	RTM-816210-B-T1-LS	RTM-816210-B-T2-LS	RTM-816210-B-T1-SLS	RTM-816210-B-T2-SLS
RTM-816215-B-T1	RTM-816215-B-T2	RTM-816215-B-T1-LS	RTM-816215-B-T2-LS	RTM-816215-B-T1-SLS	RTM-816215-B-T2-SLS
RTM-819205-B-T1	RTM-819205-B-T2	RTM-819205-B-T1-LS	RTM-819205-B-T2-LS	RTM-819205-B-T1-SLS	RTM-819205-B-T2-SLS
RTM-81927.5-B-T1	RTM-81927.5-B-T2	RTM-81927.5-B-T1-LS	RTM-81927.5-B-T2-LS	RTM-81927.5-B-T1-SLS	RTM-81927.5-B-T2-SLS
RTM-819210-B-T1	RTM-819210-B-T2	RTM-819210-B-T1-LS	RTM-819210-B-T2-LS	RTM-819210-B-T1-SLS	RTM-819210-B-T2-SLS
RTM-819215-B-T1	RTM-819215-B-T2	RTM-819215-B-T1-LS	RTM-819215-B-T2-LS	RTM-819215-B-T1-SLS	RTM-819215-B-T2-SLS
RTM-819220-B-T1	RTM-819220-B-T2	RTM-819220-B-T1-LS	RTM-819220-B-T2-LS	RTM-819220-B-T1-SLS	RTM-819220-B-T2-SLS
RTM-822205-B-T1	RTM-822205-B-T2	RTM-822205-B-T1-LS	RTM-822205-B-T2-LS	RTM-822205-B-T1-SLS	RTM-822205-B-T2-SLS
RTM-82227.5-B-T1	RTM-82227.5-B-T2	RTM-82227.5-B-T1-LS	RTM-82227.5-B-T2-LS	RTM-82227.5-B-T1-SLS	RTM-82227.5-B-T2-SLS
RTM-822210-B-T1	RTM-822210-B-T2	RTM-822210-B-T1-LS	RTM-822210-B-T2-LS	RTM-822210-B-T1-SLS	RTM-822210-B-T2-SLS
RTM-822215-B-T1	RTM-822215-B-T2	RTM-822215-B-T1-LS	RTM-822215-B-T2-LS	RTM-822215-B-T1-SLS	RTM-822215-B-T2-SLS
RTM-822220-B-T1	RTM-822220-B-T2	RTM-822220-B-T1-LS	RTM-822220-B-T2-LS	RTM-822220-B-T1-SLS	RTM-822220-B-T2-SLS
RTM-822225-B-T1	RTM-822225-B-T2	RTM-822225-B-T1-LS	RTM-822225-B-T2-LS	RTM-822225-B-T1-SLS	RTM-822225-B-T2-SLS
RTM-824205-B-T1	RTM-824205-B-T2	RTM-824205-B-T1-LS	RTM-824205-B-T2-LS	RTM-824205-B-T1-SLS	RTM-824205-B-T2-SLS
RTM-82427.5-B-T1	RTM-82427.5-B-T2	RTM-82427.5-B-T1-LS	RTM-82427.5-B-T2-LS	RTM-82427.5-B-T1-SLS	RTM-82427.5-B-T2-SLS
RTM-824210-B-T1	RTM-824210-B-T2	RTM-824210-B-T1-LS	RTM-824210-B-T2-LS	RTM-824210-B-T1-SLS	RTM-824210-B-T2-SLS
RTM-824215-B-T1	RTM-824215-B-T2	RTM-824215-B-T1-LS	RTM-824215-B-T2-LS	RTM-824215-B-T1-SLS	RTM-824215-B-T2-SLS
RTM-824220-B-T1	RTM-824220-B-T2	RTM-824220-B-T1-LS	RTM-824220-B-T2-LS	RTM-824220-B-T1-SLS	RTM-824220-B-T2-SLS
RTM-824225-B-T1	RTM-824225-B-T2	RTM-824225-B-T1-LS	RTM-824225-B-T2-LS	RTM-824225-B-T1-SLS	RTM-824225-B-T2-SLS
RTM-827205-B-T1	RTM-827205-B-T2	RTM-827205-B-T1-LS	RTM-827205-B-T2-LS	RTM-827205-B-T1-SLS	RTM-827205-B-T2-SLS
RTM-82727.5-B-T1	RTM-82727.5-B-T2	RTM-82727.5-B-T1-LS	RTM-82727.5-B-T2-LS	RTM-82727.5-B-T1-SLS	RTM-82727.5-B-T2-SLS
RTM-827210-B-T1	RTM-827210-B-T2	RTM-827210-B-T1-LS	RTM-827210-B-T2-LS	RTM-827210-B-T1-SLS	RTM-827210-B-T2-SLS
RTM-827215-B-T1	RTM-827215-B-T2	RTM-827215-B-T1-LS	RTM-827215-B-T2-LS	RTM-827215-B-T1-SLS	RTM-827215-B-T2-SLS
RTM-827220-B-T1	RTM-827220-B-T2	RTM-827220-B-T1-LS	RTM-827220-B-T2-LS	RTM-827220-B-T1-SLS	RTM-827220-B-T2-SLS
RTM-827225-B-T1	RTM-827225-B-T2	RTM-827225-B-T1-LS	RTM-827225-B-T2-LS	RTM-827225-B-T1-SLS	RTM-827225-B-T2-SLS

RTM Models Continued on Next Page



COOLING TECHNOLOGY INSTITUTE

P. O. Box 681807, Houston, Texas 77268 • 3845 Cypress Creek Parkway, Ste 420, Houston, Texas 77068
 Phone: 281.583.4087 • Fax: 281.537.1721 • email: vmanser@cti.org • http://www.cti.org

RTM Models (Note 2) Below are Modular Units with 2 Fans/Unit and 2 or 3 Air Inlet Faces/Unit

RTM-714205-D-T1	RTM-714205-D-T2	RTM-714205-D-T1-LS	RTM-714205-D-T2-LS	RTM-714205-D-T1-SLS	RTM-714205-D-T2-SLS
RTM-71427.5-D-T1	RTM-71427.5-D-T2	RTM-71427.5-D-T1-LS	RTM-71427.5-D-T2-LS	RTM-71427.5-D-T1-SLS	RTM-71427.5-D-T2-SLS
RTM-714210-D-T1	RTM-714210-D-T2	RTM-714210-D-T1-LS	RTM-714210-D-T2-LS	RTM-714210-D-T1-SLS	RTM-714210-D-T2-SLS
RTM-816205-D-T1	RTM-816205-D-T2	RTM-816205-D-T1-LS	RTM-816205-D-T2-LS	RTM-816205-D-T1-SLS	RTM-816205-D-T2-SLS
RTM-81627.5-D-T1	RTM-81627.5-D-T2	RTM-81627.5-D-T1-LS	RTM-81627.5-D-T2-LS	RTM-81627.5-D-T1-SLS	RTM-81627.5-D-T2-SLS
RTM-816210-D-T1	RTM-816210-D-T2	RTM-816210-D-T1-LS	RTM-816210-D-T2-LS	RTM-816210-D-T1-SLS	RTM-816210-D-T2-SLS
RTM-816215-D-T1	RTM-816215-D-T2	RTM-816215-D-T1-LS	RTM-816215-D-T2-LS	RTM-816215-D-T1-SLS	RTM-816215-D-T2-SLS
RTM-819205-D-T1	RTM-819205-D-T2	RTM-819205-D-T1-LS	RTM-819205-D-T2-LS	RTM-819205-D-T1-SLS	RTM-819205-D-T2-SLS
RTM-81927.5-D-T1	RTM-81927.5-D-T2	RTM-81927.5-D-T1-LS	RTM-81927.5-D-T2-LS	RTM-81927.5-D-T1-SLS	RTM-81927.5-D-T2-SLS
RTM-819210-D-T1	RTM-819210-D-T2	RTM-819210-D-T1-LS	RTM-819210-D-T2-LS	RTM-819210-D-T1-SLS	RTM-819210-D-T2-SLS
RTM-819215-D-T1	RTM-819215-D-T2	RTM-819215-D-T1-LS	RTM-819215-D-T2-LS	RTM-819215-D-T1-SLS	RTM-819215-D-T2-SLS
RTM-819220-D-T1	RTM-819220-D-T2	RTM-819220-D-T1-LS	RTM-819220-D-T2-LS	RTM-819220-D-T1-SLS	RTM-819220-D-T2-SLS
RTM-822205-D-T1	RTM-822205-D-T2	RTM-822205-D-T1-LS	RTM-822205-D-T2-LS	RTM-822205-D-T1-SLS	RTM-822205-D-T2-SLS
RTM-82227.5-D-T1	RTM-82227.5-D-T2	RTM-82227.5-D-T1-LS	RTM-82227.5-D-T2-LS	RTM-82227.5-D-T1-SLS	RTM-82227.5-D-T2-SLS
RTM-822210-D-T1	RTM-822210-D-T2	RTM-822210-D-T1-LS	RTM-822210-D-T2-LS	RTM-822210-D-T1-SLS	RTM-822210-D-T2-SLS
RTM-822215-D-T1	RTM-822215-D-T2	RTM-822215-D-T1-LS	RTM-822215-D-T2-LS	RTM-822215-D-T1-SLS	RTM-822215-D-T2-SLS
RTM-822220-D-T1	RTM-822220-D-T2	RTM-822220-D-T1-LS	RTM-822220-D-T2-LS	RTM-822220-D-T1-SLS	RTM-822220-D-T2-SLS
RTM-822225-D-T1	RTM-822225-D-T2	RTM-822225-D-T1-LS	RTM-822225-D-T2-LS	RTM-822225-D-T1-SLS	RTM-822225-D-T2-SLS
RTM-824205-D-T1	RTM-824205-D-T2	RTM-824205-D-T1-LS	RTM-824205-D-T2-LS	RTM-824205-D-T1-SLS	RTM-824205-D-T2-SLS
RTM-82427.5-D-T1	RTM-82427.5-D-T2	RTM-82427.5-D-T1-LS	RTM-82427.5-D-T2-LS	RTM-82427.5-D-T1-SLS	RTM-82427.5-D-T2-SLS
RTM-824210-D-T1	RTM-824210-D-T2	RTM-824210-D-T1-LS	RTM-824210-D-T2-LS	RTM-824210-D-T1-SLS	RTM-824210-D-T2-SLS
RTM-824215-D-T1	RTM-824215-D-T2	RTM-824215-D-T1-LS	RTM-824215-D-T2-LS	RTM-824215-D-T1-SLS	RTM-824215-D-T2-SLS
RTM-824220-D-T1	RTM-824220-D-T2	RTM-824220-D-T1-LS	RTM-824220-D-T2-LS	RTM-824220-D-T1-SLS	RTM-824220-D-T2-SLS
RTM-824225-D-T1	RTM-824225-D-T2	RTM-824225-D-T1-LS	RTM-824225-D-T2-LS	RTM-824225-D-T1-SLS	RTM-824225-D-T2-SLS
RTM-827205-D-T1	RTM-827205-D-T2	RTM-827205-D-T1-LS	RTM-827205-D-T2-LS	RTM-827205-D-T1-SLS	RTM-827205-D-T2-SLS
RTM-82727.5-D-T1	RTM-82727.5-D-T2	RTM-82727.5-D-T1-LS	RTM-82727.5-D-T2-LS	RTM-82727.5-D-T1-SLS	RTM-82727.5-D-T2-SLS
RTM-827210-D-T1	RTM-827210-D-T2	RTM-827210-D-T1-LS	RTM-827210-D-T2-LS	RTM-827210-D-T1-SLS	RTM-827210-D-T2-SLS
RTM-827215-D-T1	RTM-827215-D-T2	RTM-827215-D-T1-LS	RTM-827215-D-T2-LS	RTM-827215-D-T1-SLS	RTM-827215-D-T2-SLS
RTM-827220-D-T1	RTM-827220-D-T2	RTM-827220-D-T1-LS	RTM-827220-D-T2-LS	RTM-827220-D-T1-SLS	RTM-827220-D-T2-SLS
RTM-827225-D-T1	RTM-827225-D-T2	RTM-827225-D-T1-LS	RTM-827225-D-T2-LS	RTM-827225-D-T1-SLS	RTM-827225-D-T2-SLS

RTM Models Continued on Next Page



COOLING TECHNOLOGY INSTITUTE

P. O. Box 681807, Houston, Texas 77268 • 3845 Cypress Creek Parkway, Ste 420, Houston, Texas 77068
Phone: 281.583.4087 • Fax: 281.537.1721 • email: vmanser@cti.org • http://www.cti.org

**Reymosa Cooling Towers, Inc.
(Div. Fabrica Mexicana De Torres, S. A.)
RT Series of CTI Certified Cooling Towers
CTI Certification Validation Number C22G-13R08
August 6, 2020 (Revision 8)**

**RTM Models (Note 2) Below are Modular Units with 2 Fans/Unit and 2 or 3 Air Inlet Faces/Unit
Direct Drive (PM) Fan Motors**

RTPM-714205-B-T1	RTPM-714205-B-T2
RTPM-71427.5-B-T1	RTPM-71427.5-B-T2
RTPM-714210-B-T1	RTPM-714210-B-T2
RTPM-816205-B-T1	RTPM-816205-B-T2
RTPM-81627.5-B-T1	RTPM-81627.5-B-T2
RTPM-816210-B-T1	RTPM-816210-B-T2
RTPM-816215-B-T1	RTPM-816215-B-T2
RTPM-819205-B-T1	RTPM-819205-B-T2
RTPM-81927.5-B-T1	RTPM-81927.5-B-T2
RTPM-819210-B-T1	RTPM-819210-B-T2
RTPM-819215-B-T1	RTPM-819215-B-T2
RTPM-822205-B-T1	RTPM-822205-B-T2
RTPM-82227.5-B-T1	RTPM-82227.5-B-T2
RTPM-822210-B-T1	RTPM-822210-B-T2
RTPM-822215-B-T1	RTPM-822215-B-T2
RTPM-824205-B-T1	RTPM-824205-B-T2
RTPM-82427.5-B-T1	RTPM-82427.5-B-T2
RTPM-824210-B-T1	RTPM-824210-B-T2
RTPM-824215-B-T1	RTPM-824215-B-T2
RTPM-827205-B-T1	RTPM-827205-B-T2
RTPM-82727.5-B-T1	RTPM-82727.5-B-T2
RTPM-827210-B-T1	RTPM-827210-B-T2
RTPM-827215-B-T1	RTPM-827215-B-T2

RTM Models Continued on Next Page



COOLING TECHNOLOGY INSTITUTE

P. O. Box 681807, Houston, Texas 77268 • 3845 Cypress Creek Parkway, Ste 420, Houston, Texas 77068
Phone: 281.583.4087 • Fax: 281.537.1721 • email: vmanser@cti.org • http://www.cti.org

**Reymosa Cooling Towers, Inc.
(Div. Fabrica Mexicana De Torres, S. A.)
RT Series of CTI Certified Cooling Towers
CTI Certification Validation Number C22G-13R08
August 6, 2020 (Revision 8)**

**RTM Models (Note 2) Below are Modular Units with 2 Fans/Unit and 2 or 3 Air Inlet Faces/Unit
Direct Drive (PM) Fan Motors**

RTPM-714205-D-T1	RTPM-714205-D-T2
RTPM-71427.5-D-T1	RTPM-71427.5-D-T2
RTPM-714210-D-T1	RTPM-714210-D-T2
RTPM-816205-D-T1	RTPM-816205-D-T2
RTPM-81627.5-D-T1	RTPM-81627.5-D-T2
RTPM-816210-D-T1	RTPM-816210-D-T2
RTPM-816215-D-T1	RTPM-816215-D-T2
RTPM-819205-D-T1	RTPM-819205-D-T2
RTPM-81927.5-D-T1	RTPM-81927.5-D-T2
RTPM-819210-D-T1	RTPM-819210-D-T2
RTPM-819215-D-T1	RTPM-819215-D-T2
RTPM-822205-D-T1	RTPM-822205-D-T2
RTPM-82227.5-D-T1	RTPM-82227.5-D-T2
RTPM-822210-D-T1	RTPM-822210-D-T2
RTPM-822215-D-T1	RTPM-822215-D-T2
RTPM-824205-D-T1	RTPM-824205-D-T2
RTPM-82427.5-D-T1	RTPM-82427.5-D-T2
RTPM-824210-D-T1	RTPM-824210-D-T2
RTPM-824215-D-T1	RTPM-824215-D-T2
RTPM-827205-D-T1	RTPM-827205-D-T2
RTPM-82727.5-D-T1	RTPM-82727.5-D-T2
RTPM-827210-D-T1	RTPM-827210-D-T2
RTPM-827215-D-T1	RTPM-827215-D-T2

RTM Models Continued on Next Page



COOLING TECHNOLOGY INSTITUTE

P. O. Box 681807, Houston, Texas 77268 • 3845 Cypress Creek Parkway, Ste 420, Houston, Texas 77068
Phone: 281.583.4087 • Fax: 281.537.1721 • email: vmanser@cti.org • http://www.cti.org

**Reymosa Cooling Towers, Inc.
(Div. Fabrica Mexicana De Torres, S. A.)
RT Series of CTI Certified Cooling Towers
CTI Certification Validation Number C22G-13R08
August 6, 2020 (Revision 8)**

**RTM Models (Note 2) Below are Modular Units with Gear Drive and 1 Fan/Unit and 2 or 3 Air Inlet Faces/Unit
8 foot Width Units**

RTGM-812103-B-T1	RTGM-812103-B-T2
RTGM-812105-B-T1	RTGM-812105-B-T2
RTGM-81217.5-B-T1	RTGM-81217.5-B-T2
RTGM-812110-B-T1	RTGM-812110-B-T2
RTGM-812115-B-T1	RTGM-812115-B-T2
RTGM-812120-B-T1	RTGM-812120-B-T2
RTGM-812125-B-T1	RTGM-812125-B-T2
RTGM-812130-B-T1	RTGM-812130-B-T2
RTGM-812103-D-T1	RTGM-812103-D-T2
RTGM-812105-D-T1	RTGM-812105-D-T2
RTGM-81217.5-D-T1	RTGM-81217.5-D-T2
RTGM-812110-D-T1	RTGM-812110-D-T2
RTGM-812115-D-T1	RTGM-812115-D-T2
RTGM-812120-D-T1	RTGM-812120-D-T2
RTGM-812125-D-T1	RTGM-812125-D-T2
RTGM-812130-D-T1	RTGM-812130-D-T2

RTM Models Continued on Next Page



COOLING TECHNOLOGY INSTITUTE

P. O. Box 681807, Houston, Texas 77268 • 3845 Cypress Creek Parkway, Ste 420, Houston, Texas 77068
Phone: 281.583.4087 • Fax: 281.537.1721 • email: vmanser@cti.org • http://www.cti.org

RTM Models (Note 2) Below are Modular Units with Gear Drive and 1 Fan/Unit and 2 or 3 Air Inlet Faces/Unit 10 foot Width Units

RTGM-1012103-B-T1	RTGM-1012103-B-T2	RTGM-1012103-D-T1	RTGM-1012103-D-T2
RTGM-1012105-B-T1	RTGM-1012105-B-T2	RTGM-1012105-D-T1	RTGM-1012105-D-T2
RTGM-101217.5-B-T1	RTGM-101217.5-B-T2	RTGM-101217.5-D-T1	RTGM-101217.5-D-T2
RTGM-1012110-B-T1	RTGM-1012110-B-T2	RTGM-1012110-D-T1	RTGM-1012110-D-T2
RTGM-1012115-B-T1	RTGM-1012115-B-T2	RTGM-1012115-D-T1	RTGM-1012115-D-T2
RTGM-1012120-B-T1	RTGM-1012120-B-T2	RTGM-1012120-D-T1	RTGM-1012120-D-T2
RTGM-1012125-B-T1	RTGM-1012125-B-T2	RTGM-1012125-D-T1	RTGM-1012125-D-T2
RTGM-1012130-B-T1	RTGM-1012130-B-T2	RTGM-1012130-D-T1	RTGM-1012130-D-T2
RTGM-1014103-B-T1	RTGM-1014103-B-T2	RTGM-1014103-D-T1	RTGM-1014103-D-T2
RTGM-1014105-B-T1	RTGM-1014105-B-T2	RTGM-1014105-D-T1	RTGM-1014105-D-T2
RTGM-101417.5-B-T1	RTGM-101417.5-B-T2	RTGM-101417.5-D-T1	RTGM-101417.5-D-T2
RTGM-1014110-B-T1	RTGM-1014110-B-T2	RTGM-1014110-D-T1	RTGM-1014110-D-T2
RTGM-1014115-B-T1	RTGM-1014115-B-T2	RTGM-1014115-D-T1	RTGM-1014115-D-T2
RTGM-1014120-B-T1	RTGM-1014120-B-T2	RTGM-1014120-D-T1	RTGM-1014120-D-T2
RTGM-1014125-B-T1	RTGM-1014125-B-T2	RTGM-1014125-D-T1	RTGM-1014125-D-T2
RTGM-1014130-B-T1	RTGM-1014130-B-T2	RTGM-1014130-D-T1	RTGM-1014130-D-T2
		RTGM-1014140-D-T1	RTGM-1014140-D-T2
RTGM-1016103-B-T1	RTGM-1016103-B-T2	RTGM-1016103-D-T1	RTGM-1016103-D-T2
RTGM-1016105-B-T1	RTGM-1016105-B-T2	RTGM-1016105-D-T1	RTGM-1016105-D-T2
RTGM-101617.5-B-T1	RTGM-101617.5-B-T2	RTGM-101617.5-D-T1	RTGM-101617.5-D-T2
RTGM-1016110-B-T1	RTGM-1016110-B-T2	RTGM-1016110-D-T1	RTGM-1016110-D-T2
RTGM-1016115-B-T1	RTGM-1016115-B-T2	RTGM-1016115-D-T1	RTGM-1016115-D-T2
RTGM-1016120-B-T1	RTGM-1016120-B-T2	RTGM-1016120-D-T1	RTGM-1016120-D-T2
RTGM-1016125-B-T1	RTGM-1016125-B-T2	RTGM-1016125-D-T1	RTGM-1016125-D-T2
RTGM-1016130-B-T1	RTGM-1016130-B-T2	RTGM-1016130-D-T1	RTGM-1016130-D-T2
RTGM-1016140-B-T1	RTGM-1016140-B-T2	RTGM-1016140-D-T1	RTGM-1016140-D-T2
RTGM-1018103-B-T1	RTGM-1018103-B-T2	RTGM-1018103-D-T1	RTGM-1018103-D-T2
RTGM-1018105-B-T1	RTGM-1018105-B-T2	RTGM-1018105-D-T1	RTGM-1018105-D-T2
RTGM-101817.5-B-T1	RTGM-101817.5-B-T2	RTGM-101817.5-D-T1	RTGM-101817.5-D-T2
RTGM-1018110-B-T1	RTGM-1018110-B-T2	RTGM-1018110-D-T1	RTGM-1018110-D-T2
RTGM-1018115-B-T1	RTGM-1018115-B-T2	RTGM-1018115-D-T1	RTGM-1018115-D-T2
RTGM-1018120-B-T1	RTGM-1018120-B-T2	RTGM-1018120-D-T1	RTGM-1018120-D-T2
RTGM-1018125-B-T1	RTGM-1018125-B-T2	RTGM-1018125-D-T1	RTGM-1018125-D-T2
RTGM-1018130-B-T1	RTGM-1018130-B-T2	RTGM-1018130-D-T1	RTGM-1018130-D-T2
RTGM-1018140-B-T1	RTGM-1018140-B-T2	RTGM-1018140-D-T1	RTGM-1018140-D-T2
		RTGM-1018150-D-T1	RTGM-1018150-D-T2
RTGM-1020103-B-T1	RTGM-1020103-B-T2	RTGM-1020103-D-T1	RTGM-1020103-D-T2
RTGM-1020105-B-T1	RTGM-1020105-B-T2	RTGM-1020105-D-T1	RTGM-1020105-D-T2
RTGM-102017.5-B-T1	RTGM-102017.5-B-T2	RTGM-102017.5-D-T1	RTGM-102017.5-D-T2
RTGM-1020110-B-T1	RTGM-1020110-B-T2	RTGM-1020110-D-T1	RTGM-1020110-D-T2
RTGM-1020115-B-T1	RTGM-1020115-B-T2	RTGM-1020115-D-T1	RTGM-1020115-D-T2
RTGM-1020120-B-T1	RTGM-1020120-B-T2	RTGM-1020120-D-T1	RTGM-1020120-D-T2
RTGM-1020125-B-T1	RTGM-1020125-B-T2	RTGM-1020125-D-T1	RTGM-1020125-D-T2
RTGM-1020130-B-T1	RTGM-1020130-B-T2	RTGM-1020130-D-T1	RTGM-1020130-D-T2
RTGM-1020140-B-T1	RTGM-1020140-B-T2	RTGM-1020140-D-T1	RTGM-1020140-D-T2
RTGM-1020150-B-T1	RTGM-1020150-B-T2	RTGM-1020150-D-T1	RTGM-1020150-D-T2
		RTGM-1020160-D-T1	RTGM-1020160-D-T2

RTM Models Continued on Next Page



COOLING TECHNOLOGY INSTITUTE

P. O. Box 681807, Houston, Texas 77268 • 3845 Cypress Creek Parkway, Ste 420, Houston, Texas 77068
Phone: 281.583.4087 • Fax: 281.537.1721 • email: vmanser@cti.org • http://www.cti.org

RTM Models (Note 2) Below are Modular Units with Gear Drive and 1 Fan/Unit and 2 or 3 Air Inlet Faces/Unit 12 foot Width Units

RTGM-1212105-B-T1	RTGM-1212105-B-T2	RTGM-1212105-D-T1	RTGM-1212105-D-T2
RTGM-121217.5-B-T1	RTGM-121217.5-B-T2	RTGM-121217.5-D-T1	RTGM-121217.5-D-T2
RTGM-1212110-B-T1	RTGM-1212110-B-T2	RTGM-1212110-D-T1	RTGM-1212110-D-T2
RTGM-1212115-B-T1	RTGM-1212115-B-T2	RTGM-1212115-D-T1	RTGM-1212115-D-T2
RTGM-1212120-B-T1	RTGM-1212120-B-T2	RTGM-1212120-D-T1	RTGM-1212120-D-T2
RTGM-1212125-B-T1	RTGM-1212125-B-T2	RTGM-1212125-D-T1	RTGM-1212125-D-T2
RTGM-1212130-B-T1	RTGM-1212130-B-T2	RTGM-1212130-D-T1	RTGM-1212130-D-T2
		RTGM-1212140-D-T1	RTGM-1212140-D-T2
RTGM-1214105-B-T1	RTGM-1214105-B-T2	RTGM-1214105-D-T1	RTGM-1214105-D-T2
RTGM-121417.5-B-T1	RTGM-121417.5-B-T2	RTGM-121417.5-D-T1	RTGM-121417.5-D-T2
RTGM-1214110-B-T1	RTGM-1214110-B-T2	RTGM-1214110-D-T1	RTGM-1214110-D-T2
RTGM-1214115-B-T1	RTGM-1214115-B-T2	RTGM-1214115-D-T1	RTGM-1214115-D-T2
RTGM-1214120-B-T1	RTGM-1214120-B-T2	RTGM-1214120-D-T1	RTGM-1214120-D-T2
RTGM-1214125-B-T1	RTGM-1214125-B-T2	RTGM-1214125-D-T1	RTGM-1214125-D-T2
RTGM-1214130-B-T1	RTGM-1214130-B-T2	RTGM-1214130-D-T1	RTGM-1214130-D-T2
RTGM-1214140-B-T1	RTGM-1214140-B-T2	RTGM-1214140-D-T1	RTGM-1214140-D-T2
		RTGM-1214150-D-T1	RTGM-1214150-D-T2
RTGM-1216105-B-T1	RTGM-1216105-B-T2	RTGM-1216105-D-T1	RTGM-1216105-D-T2
RTGM-121617.5-B-T1	RTGM-121617.5-B-T2	RTGM-121617.5-D-T1	RTGM-121617.5-D-T2
RTGM-1216110-B-T1	RTGM-1216110-B-T2	RTGM-1216110-D-T1	RTGM-1216110-D-T2
RTGM-1216115-B-T1	RTGM-1216115-B-T2	RTGM-1216115-D-T1	RTGM-1216115-D-T2
RTGM-1216120-B-T1	RTGM-1216120-B-T2	RTGM-1216120-D-T1	RTGM-1216120-D-T2
RTGM-1216125-B-T1	RTGM-1216125-B-T2	RTGM-1216125-D-T1	RTGM-1216125-D-T2
RTGM-1216130-B-T1	RTGM-1216130-B-T2	RTGM-1216130-D-T1	RTGM-1216130-D-T2
RTGM-1216140-B-T1	RTGM-1216140-B-T2	RTGM-1216140-D-T1	RTGM-1216140-D-T2
		RTGM-1216150-D-T1	RTGM-1216150-D-T2
RTGM-1218105-B-T1	RTGM-1218105-B-T2	RTGM-1218105-D-T1	RTGM-1218105-D-T2
RTGM-121817.5-B-T1	RTGM-121817.5-B-T2	RTGM-121817.5-D-T1	RTGM-121817.5-D-T2
RTGM-1218110-B-T1	RTGM-1218110-B-T2	RTGM-1218110-D-T1	RTGM-1218110-D-T2
RTGM-1218115-B-T1	RTGM-1218115-B-T2	RTGM-1218115-D-T1	RTGM-1218115-D-T2
RTGM-1218120-B-T1	RTGM-1218120-B-T2	RTGM-1218120-D-T1	RTGM-1218120-D-T2
RTGM-1218125-B-T1	RTGM-1218125-B-T2	RTGM-1218125-D-T1	RTGM-1218125-D-T2
RTGM-1218130-B-T1	RTGM-1218130-B-T2	RTGM-1218130-D-T1	RTGM-1218130-D-T2
RTGM-1218140-B-T1	RTGM-1218140-B-T2	RTGM-1218140-D-T1	RTGM-1218140-D-T2
RTGM-1218150-B-T1	RTGM-1218150-B-T2	RTGM-1218150-D-T1	RTGM-1218150-D-T2
		RTGM-1218160-D-T1	RTGM-1218160-D-T2
RTGM-1220105-B-T1	RTGM-1220105-B-T2	RTGM-1220105-D-T1	RTGM-1220105-D-T2
RTGM-122017.5-B-T1	RTGM-122017.5-B-T2	RTGM-122017.5-D-T1	RTGM-122017.5-D-T2
RTGM-1220110-B-T1	RTGM-1220110-B-T2	RTGM-1220110-D-T1	RTGM-1220110-D-T2
RTGM-1220115-B-T1	RTGM-1220115-B-T2	RTGM-1220115-D-T1	RTGM-1220115-D-T2
RTGM-1220120-B-T1	RTGM-1220120-B-T2	RTGM-1220120-D-T1	RTGM-1220120-D-T2
RTGM-1220125-B-T1	RTGM-1220125-B-T2	RTGM-1220125-D-T1	RTGM-1220125-D-T2
RTGM-1220130-B-T1	RTGM-1220130-B-T2	RTGM-1220130-D-T1	RTGM-1220130-D-T2
RTGM-1220140-B-T1	RTGM-1220140-B-T2	RTGM-1220140-D-T1	RTGM-1220140-D-T2
RTGM-1220150-B-T1	RTGM-1220150-B-T2	RTGM-1220150-D-T1	RTGM-1220150-D-T2
RTGM-1220160-B-T1	RTGM-1220160-B-T2	RTGM-1220160-D-T1	RTGM-1220160-D-T2
		RTGM-1220175-D-T1	RTGM-1220175-D-T2
RTGM-1222105-B-T1	RTGM-1222105-B-T2	RTGM-1222105-D-T1	RTGM-1222105-D-T2
RTGM-122217.5-B-T1	RTGM-122217.5-B-T2	RTGM-122217.5-D-T1	RTGM-122217.5-D-T2
RTGM-1222110-B-T1	RTGM-1222110-B-T2	RTGM-1222110-D-T1	RTGM-1222110-D-T2
RTGM-1222115-B-T1	RTGM-1222115-B-T2	RTGM-1222115-D-T1	RTGM-1222115-D-T2
RTGM-1222120-B-T1	RTGM-1222120-B-T2	RTGM-1222120-D-T1	RTGM-1222120-D-T2
RTGM-1222125-B-T1	RTGM-1222125-B-T2	RTGM-1222125-D-T1	RTGM-1222125-D-T2
RTGM-1222130-B-T1	RTGM-1222130-B-T2	RTGM-1222130-D-T1	RTGM-1222130-D-T2
RTGM-1222140-B-T1	RTGM-1222140-B-T2	RTGM-1222140-D-T1	RTGM-1222140-D-T2
RTGM-1222150-B-T1	RTGM-1222150-B-T2	RTGM-1222150-D-T1	RTGM-1222150-D-T2
RTGM-1222160-B-T1	RTGM-1222160-B-T2	RTGM-1222160-D-T1	RTGM-1222160-D-T2
RTGM-1222175-B-T1	RTGM-1222175-B-T2	RTGM-1222175-D-T1	RTGM-1222175-D-T2

RTM Models Continued Next Page



COOLING TECHNOLOGY INSTITUTE

P. O. Box 681807, Houston, Texas 77268 • 3845 Cypress Creek Parkway, Ste 420, Houston, Texas 77068
Phone: 281.583.4087 • Fax: 281.537.1721 • email: vmanser@cti.org • http://www.cti.org

**Reymosa Cooling Towers, Inc.
(Div. Fabrica Mexicana De Torres, S. A.)
RT Series of CTI Certified Cooling Towers
CTI Certification Validation Number C22G-13R08
August 6, 2020 (Revision 8)**

**RTM Models (Note 2) Below are Modular Units with Gear Drive and 1 Fan/Unit and 2 or 3 Air Inlet Faces/Unit
12 foot Width Units**

RTGM-1223110-E-T1	RTGM-1223110-E-T2
RTGM-1223115-E-T1	RTGM-1223115-E-T2
RTGM-1223120-E-T1	RTGM-1223120-E-T2
RTGM-1223125-E-T1	RTGM-1223125-E-T2
RTGM-1223130-E-T1	RTGM-1223130-E-T2
RTGM-1223140-E-T1	RTGM-1223140-E-T2
RTGM-1223150-E-T1	RTGM-1223150-E-T2
RTGM-1223160-E-T1	RTGM-1223160-E-T2

RTM Models Concluded



COOLING TECHNOLOGY INSTITUTE

P. O. Box 681807, Houston, Texas 77268 • 3845 Cypress Creek Parkway, Ste 420, Houston, Texas 77068
 Phone: 281.583.4087 • Fax: 281.537.1721 • email: vmanser@cti.org • http://www.cti.org

Reymosa Cooling Towers, Inc.
(Div. Fabrica Mexicana De Torres, S. A.)
RT Series of CTI Certified Cooling Towers
CTI Certification Validation Number C22G-13R08
August 6, 2020 (Revision 8)

**RTU Models (Note 3) Below are Reduced Height Units with 1, 2 or 4 Fans/Unit
 and 4 Air Inlets Faces/Unit**

RTU-30311.5-A	RTU-709103-A	RTU-812103-A	RTU-819203-A	RTU-1414403-A	RTU-1622405-A
RTU-303102-A	RTU-709103-A-LS	RTU-812103-A-LS	RTU-819203-A-LS	RTU-1414403-A-LS	RTU-1622405-A-LS
	RTU-709103-A-SLS	RTU-812103-A-SLS	RTU-819203-A-SLS	RTU-1414403-A-SLS	RTU-1622405-A-SLS
RTU-404103-A	RTU-709105-A	RTU-812105-A	RTU-819205-A	RTU-1414405-A	RTU-162247.5-A
RTU-404105-A	RTU-709105-A-LS	RTU-812105-A-LS	RTU-819205-A-LS	RTU-1414405-A-LS	RTU-162247.5-A-LS
	RTU-709105-A-SLS	RTU-812105-A-SLS	RTU-819205-A-SLS	RTU-1414405-A-SLS	RTU-162247.5-A-SLS
RTU-505103-A	RTU-70917.5-A	RTU-81217.5-A	RTU-81927.5-A	RTU-141447.5-A	RTU-1622410-A
RTU-505105-A	RTU-70917.5-A-LS	RTU-81217.5-A-LS	RTU-81927.5-A-LS	RTU-141447.5-A-LS	RTU-1622410-A-LS
	RTU-70917.5-A-SLS	RTU-81217.5-A-SLS	RTU-81927.5-A-SLS	RTU-141447.5-A-SLS	RTU-1622410-A-SLS
RTU-606103-A	RTU-709110-A	RTU-812110-A	RTU-819210-A	RTU-1414410-A	RTU-1622415-A
RTU-606105-A	RTU-709110-A-LS	RTU-812110-A-LS	RTU-819210-A-LS	RTU-1414410-A-LS	RTU-1622415-A-LS
RTU-60617.5-A	RTU-709110-A-SLS	RTU-812110-A-SLS	RTU-819210-A-SLS	RTU-1414410-A-SLS	RTU-1622415-A-SLS
	RTU-709115-A	RTU-812115-A	RTU-819215-A		RTU-1622420-A
RTU-707103-A	RTU-709115-A-LS	RTU-812115-A-LS	RTU-819215-A-LS	RTU-1616403-A	RTU-1622420-A-LS
RTU-707103-A-LS	RTU-709115-A-SLS	RTU-812115-A-SLS	RTU-819215-A-SLS	RTU-1616403-A-LS	RTU-1622420-A-SLS
RTU-707103-A-SLS		RTU-812120-A	RTU-819220-A	RTU-1616403-A-SLS	
RTU-707105-A	RTU-808103-A	RTU-812120-A-LS	RTU-819220-A-LS	RTU-1616405-A	RTU-1624405-A
RTU-707105-A-LS	RTU-808103-A-LS	RTU-812120-A-SLS	RTU-819220-A-SLS	RTU-1616405-A-LS	RTU-1624405-A-LS
RTU-707105-A-SLS	RTU-808103-A-SLS	RTU-812125-A		RTU-1616405-A-SLS	RTU-1624405-A-SLS
RTU-70717.5-A	RTU-808105-A	RTU-812125-A-LS	RTU-822205-A	RTU-161647.5-A	RTU-162447.5-A
RTU-70717.5-A-LS	RTU-808105-A-LS	RTU-812125-A-SLS	RTU-822205-A-LS	RTU-161647.5-A-LS	RTU-162447.5-A-LS
RTU-70717.5-A-SLS	RTU-808105-A-SLS		RTU-822205-A-SLS	RTU-161647.5-A-SLS	RTU-162447.5-A-SLS
RTU-707110-A	RTU-80817.5-A	RTU-714203-A	RTU-82227.5-A	RTU-1616410-A	RTU-1624410-A
RTU-707110-A-LS	RTU-80817.5-A-LS	RTU-714203-A-LS	RTU-82227.5-A-LS	RTU-1616410-A-LS	RTU-1624410-A-LS
RTU-707110-A-SLS	RTU-80817.5-A-SLS	RTU-714203-A-SLS	RTU-82227.5-A-SLS	RTU-1616410-A-SLS	RTU-1624410-A-SLS
	RTU-808110-A	RTU-714205-A	RTU-822210-A	RTU-1616415-A	RTU-1624415-A
RTU-708103-A	RTU-808110-A-LS	RTU-714205-A-LS	RTU-822210-A-LS	RTU-1616415-A-LS	RTU-1624415-A-LS
RTU-708103-A-LS	RTU-808110-A-SLS	RTU-714205-A-SLS	RTU-822210-A-SLS	RTU-1616415-A-SLS	RTU-1624415-A-SLS
RTU-708103-A-SLS	RTU-808115-A	RTU-71427.5-A	RTU-822215-A		RTU-1624420-A
RTU-708105-A	RTU-808115-A-LS	RTU-71427.5-A-LS	RTU-822215-A-LS	RTU-1619403-A	RTU-1624420-A-LS
RTU-708105-A-LS	RTU-808115-A-SLS	RTU-71427.5-A-SLS	RTU-822215-A-SLS	RTU-1619403-A-LS	RTU-1624420-A-SLS
RTU-708105-A-SLS		RTU-714210-A	RTU-822220-A	RTU-1619403-A-SLS	
RTU-70817.5-A	RTU-810103-A	RTU-714210-A-LS	RTU-822220-A-LS	RTU-1619405-A	
RTU-70817.5-A-LS	RTU-810103-A-LS	RTU-714210-A-SLS	RTU-822220-A-SLS	RTU-1619405-A-LS	
RTU-70817.5-A-SLS	RTU-810103-A-SLS			RTU-1619405-A-SLS	
RTU-708110-A	RTU-810105-A	RTU-816203-A	RTU-824205-A	RTU-161947.5-A	
RTU-708110-A-LS	RTU-810105-A-LS	RTU-816203-A-LS	RTU-824205-A-LS	RTU-161947.5-A-LS	
RTU-708110-A-SLS	RTU-810105-A-SLS	RTU-816203-A-SLS	RTU-824205-A-SLS	RTU-161947.5-A-SLS	
RTU-708115-A	RTU-81017.5-A	RTU-816205-A	RTU-82427.5-A	RTU-1619410-A	
RTU-708115-A-LS	RTU-81017.5-A-LS	RTU-816205-A-LS	RTU-82427.5-A-LS	RTU-1619410-A-LS	
RTU-708115-A-SLS	RTU-81017.5-A-SLS	RTU-816205-A-SLS	RTU-82427.5-A-SLS	RTU-1619410-A-SLS	
	RTU-810110-A	RTU-81627.5-A	RTU-824210-A	RTU-1619415-A	
	RTU-810110-A-LS	RTU-81627.5-A-LS	RTU-824210-A-LS	RTU-1619415-A-LS	
	RTU-810110-A-SLS	RTU-81627.5-A-SLS	RTU-824210-A-SLS	RTU-1619415-A-SLS	
	RTU-810115-A	RTU-816210-A	RTU-824215-A	RTU-1619420-A	
	RTU-810115-A-LS	RTU-816210-A-LS	RTU-824215-A-LS	RTU-1619420-A-LS	
	RTU-810115-A-SLS	RTU-816210-A-SLS	RTU-824215-A-SLS	RTU-1619420-A-SLS	
	RTU-810120-A	RTU-816215-A	RTU-824220-A		
	RTU-810120-A-LS	RTU-816215-A-LS	RTU-824220-A-LS		
	RTU-810120-A-SLS	RTU-816215-A-SLS	RTU-824220-A-SLS		

RTU Models Continued Next Page



COOLING TECHNOLOGY INSTITUTE

P. O. Box 681807, Houston, Texas 77268 • 3845 Cypress Creek Parkway, Ste 420, Houston, Texas 77068
 Phone: 281.583.4087 • Fax: 281.537.1721 • email: vmanser@cti.org • http://www.cti.org

Reymosa Cooling Towers, Inc.
(Div. Fabrica Mexicana De Torres, S. A.)
RT Series of CTI Certified Cooling Towers
CTI Certification Validation Number C22G-13R08
August 6, 2020 (Revision 8)

RTU Models (Note 3) Below are Reduced Height Units with 1, 2 or 4 Fans/Unit
Direct Drive (PM) Fan Motors

RTUP-707105-A	RTUP-812105-A	RTUP-1414405-A
RTUP-70717.5-A	RTUP-81217.5-A	RTUP-141447.5-A
RTUP-707110-A	RTUP-812110-A	RTUP-1414410-A
	RTUP-812115-A	
RTUP-708105-A		RTUP-1616405-A
RTUP-70817.5-A	RTUP-816205-A	RTUP-161647.5-A
RTUP-708110-A	RTUP-81627.5-A	RTUP-1616410-A
	RTUP-816210-A	
RTUP-709105-A		RTUP-1619405-A
RTUP-70917.5-A	RTUP-819205-A	RTUP-161947.5-A
RTUP-709110-A	RTUP-81927.5-A	RTUP-1619410-A
RTUP-709115-A	RTUP-819210-A	RTUP-1619415-A
	RTUP-819215-A	
RTUP-714205-A		RTUP-1622405-A
RTUP-71427.5-A	RTUP-822205-A	RTUP-162247.5-A
RTUP-714210-A	RTUP-82227.5-A	RTUP-1622410-A
	RTUP-822210-A	RTUP-1622415-A
	RTUP-822215-A	
RTUP-808105-A		RTUP-1624405-A
RTUP-80817.5-A	RTUP-824205-A	RTUP-162447.5-A
RTUP-808110-A	RTUP-82427.5-A	RTUP-1624410-A
	RTUP-824210-A	RTUP-1624415-A
RTUP-810105-A	RTUP-824215-A	
RTUP-81017.5-A		
RTUP-810110-A		
RTUP-810115-A		

RT Models Concluded



COOLING TECHNOLOGY INSTITUTE

P. O. Box 681807, Houston, Texas 77268 • 3845 Cypress Creek Parkway, Ste 420, Houston, Texas 77068
Phone: 281.583.4087 • Fax: 281.537.1721 • email: vmanser@cti.org • http://www.cti.org

Reymosa Cooling Towers, Inc.
(Div. Fabrica Mexicana De Torres, S. A.)
RT Series of CTI Certified Cooling Towers
CTI Certification Validation Number C22G-13R08
August 6, 2020 (Revision 8)

Footnotes:

1. RT models are single units with 1, 2 or 4 fans/unit and 4 air inlet faces/unit. RTG models are single-fan with gear drive or alternate, permanent-magnet (PM) motor drive.
2. RTM models are modular units intended to be mounted adjacent to each other. RTGM models are single fan with gear drive or alternate, permanent-magnet (PM) motor drive.
 - _T1 indicates number of T1 type modules with 2 air inlets on long sides of unit (-S orientation) or 3 air inlets on 2 long sides and 1 short side per module (-S orientation) or 3 air inlets on 1 long side and 2 short sides per module (-L orientation)
 - _T2 indicates number of T2 type modules with 2 open air inlets per module
 - L inserted in model numbers indicates orientation with long axis of modules side-by-side
 - S inserted in model numbers indicates orientation with short axis of modules side-by-side
 - X inserted in model numbers for two or four-module arrangements having one long side and one short side open per module
3. RTU models are reduced height units with 1, 2 or 4 fans/unit and 4 inlet faces/unit. All units have the –A fill configuration (note 4, below).
4. RTP, RTPM, RTUP are prefixes used on standard models with direct drive by permanent magnet (PM) fan motors.
5. The -A, -B, -C, -D and -E in the model numbers above indicates the heat transfer fill configuration.
6. The -LS and -SLS in the model numbers above indicates the fan type configuration:
 - No suffix indicates standard fan
 - LS indicates low sound fan option
 - SLS indicates super low sound fan option
7. Certification includes units with water inlet configuration on side or end faces
8. Certification includes optional shaft-driven gear box with motor outside the air stream (suffix –OM)
9. Suffix -Y is added to the model number to indicate units that are not CTI certified due to tower installation locations, applications or modifications that affect thermal capacity.
10. No additional suffix is used for accessories or modifications that do not affect thermal capacity.
11. Sample RT model number: RT-714210-B-LS (a single unit)
 - Where: RT = Product series name, Single unit
 - 7 = Unit width
 - 14 = Unit length
 - 2 = Number of fans
 - 10 = Fan motor power
 - B = Fill configuration
 - LS = Fan type
12. Sample RTM model number: RTM-816215-D-1T1-2T2-1T1-L-SLS (a 4 module unit)
 - Where: RTM = Product series name, Modular unit
 - 8 = Unit width
 - 16 = Unit length
 - 2 = Number of fans
 - 15 = Fan motor power
 - D = Fill configuration
 - 1T1-2T2-1T1 = Type of modules and installation sequence = one T1 + two T2 + one T1 module
 - L = Orientation with long axis of units side-by-side
 - SLS = Fan type